REV.	DATE	DESCRIPTION	BY	C'K'D'

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE



EUROPEAN PROJECTION

PERFORMANCE CHARACTERISTICS

- OPERATING TEMPERATURE : -55 °C TO +125 °C.
- INSULATION RESISTANCE : 5000 MΩ MIN.
- TEST POTENTIAL : 2000 V EFF.(SIGNAL) - 4000 V EFF> (POWER)
- CONNECTOR AS PER VDE 0110 CLASS III - POLLUTION DEGREE 3: 830 V AC EFF. (POWER CONTACTS)

MATERIAL

- BODY : GLASS-FILLED POLYESTER UL94-V0
  COLOUR : BLACK.
- TRILOK RING: HIGH STRENGTH CUZN ALLOY, NI PLATED

NOTES

1. CONTACTS TO BE ORDERED SEPARATELY
2. ACCEPTS Ø3.6MM MACHINED (POWER) AND Ø1.6MM MACHINED OR STAMPED AND FORMED (SIGN.) CONTACTS
3. CONNECTOR TO BE MATED WITH UTG62411SN

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90
INT. ST.	10 11	12 13	14 18	20 31	32 33	34 38	39 40	42 43	44 45	46 48	56 70	72 73	75 76	81 82 83 84 88

1DEC ±0,2 1DEC
2DEC ±0,1 2DEC
ANGLES ±1° HOEKEN

WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.

ALL DIMENSIONS IN MM

ALLE AFMETINGEN IN MM

APPR.	DATE	SIGN.
DRAFT	14-11-01	P BUYCKX
CHECKED		
PROD. MGR.		
PR.ENG.MGR.		
PR.MGT.MGR.		

REFERENCES / REFERENTIES

MALE RECEPTACLE 4 POWER Ø3.6 CONTACTS

CAT. No. UTG02411P

SOURIAU
Connection Technology

SOURIAU
Route Nationale 23
72470 CHAMPAGNE

SCALE

BS,A ,203025,000 — DRAWING NR.
CUSTOMER DRAWING
0A — REVISION

NOT EXPORT CONTROLLED

BS,A ,203025,000 0A

19-Dec-2002 17:03:42