



jalas® VIP 2108

EN ISO 20345:2011 S3, SRA, HRO ASTM F2413-18 M/I/C SD 35 PR

Learn more

Safety shoe, nail protection material plasma-treated composite (PTC) textile, toecap material steel, rubber outsole, upper material full-grain leather.

CHARACTERISTICS

- Excellent shock absorption
- Good fit
- Comfortable

FUNCTIONS

- Anti-static properties
- Ventilating insole
- Water repellent leather
- Specially designed details
- Shock absorbing
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

prevents risk of: , toe injuries, nail penetration, sprain injuries, antistatic, strain injuries

PRIMARY ENVIRONMENTS OF USE

outdoors, indoors, office environments, environments with risk for outsole penetration, dry environments, clean environments

PRIMARY AREAS OF USE

engineering, office work

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Narrow/Regular
COLLECTION VIP
UPPER MATERIAL Full-grain leather
TOECAP MATERIAL Steel
LINING MATERIAL Leather
INSOLE FX2 VIP Safety
INNERSOLE MATERIAL Leather, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in Poron® XRD®
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces
COLOUR Black
NET WEIGHT, (SIZE 42) 1.4 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 20345:2011
S3, SRA, HRO

ASTM F2413-18
M/I/C
SD 35 PR

ÖNORM Z 1259

DGUV 112-191

FEATURES

- Anti-static properties
- ESD
- Water repellent
- Oil-resistant outsole
- Nail protection in plasma-treated composite (PTC) textile
- Shock absorbing
- Steel toecap

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3½	4	2108-35	6408487509995
36	3	4	5	2108-36	6408487510007
37	4	5	6	2108-37	6408487510014
38	5	5½	6½	2108-38	6408487510021
39	6	6½	7½	2108-39	6408487510038
40	6½	7½	8½	2108-40	6408487510045
41	7	8	9	2108-41	6408487510052
42	8	9	10	2108-42	6408487510069
43	9	9½	11	2108-43	6408487510076
44	10	10½	11½	2108-44	6408487510083
45	10½	11	12½	2108-45	6408487510090
46	11	12	13	2108-46	6408487510106
47	12	13	14	2108-47	6408487510113
48	13	13½	14½	2108-48	6408487510120

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.