

Product data sheet

uvex pronamic/ uvex pronamic E



Product characteristics:

- side Euroslot adapters (30 mm) for attaching earmuffs and the pronamic visor system
- additional elements allow a wide range of accessories to be attached to the helmet
- shorter brim for a wider field of vision (all S-versions)
- adjustable air vents for maximum ventilation (uvex pronamic B)
- completely closed helmet shell (uvex pronamic E)
- pre-mounted four-point chin strap (9790021)
- chinstrap-/ goggle-clip (9790022) for positioning the chin strap in the parking position
- suspension harness (9790310) fitted with wheel ratchet system for variable width adjustment with the sweatband (9790311)
- six-point textile band attachment ensures an optimal fit and maximum comfort
- enlarged neck support
- adapter for the IES spectacle clip included as standard

Standards and requirements:

The uvex pronamic series meets the requirements of Regulation 2016/425 and is CE marked.

They meet the harmonized standards EN 50365:2002 (uvex pronamic E) and EN 397:2012+A1:2012 as well as their optional requirement low temperatures (-30°C).

This PPE is subject to the conformity assessment procedure and is monitored by:

PZT GmbH, Bismarckstraße 264 B,
26389 Wilhelmshaven, Germany
(notified body number 1974)

The applicable jurisdiction can be found on the Declaration of Conformity.

You can find this under: uvex-safety.com/ce

Technical data:

Sizes:	51 to 65cm
Interior:	Head ring with wheel ratchet system with six-point textile straps
Weight:	pronamic B-WR: 405g pronamic B-S-WR: 402g pronamic S-KR: 446g pronamic E-WR: 396g pronamic E-S-WR: 394g

Materials:

Helmet shell:	HDPE
Headband:	PE
Sweatband:	Synthetic leather

Use and storage:

Operating temperature:	-30 °C to +50 °C
Operating time:	4 years from the date of first use
Recommended storage conditions:	Store helmet dry (storage temperature 20 °C ± 15 °C) and out of direct sunlight in original packaging
Storage time:	4 years from the date of production

Variants/colors:

uvex pronamic B-WR

Article-Nr.	Designation	Color	Packaging unit
9731030	pronamic B-WR white	white	1 piece
9731130	pronamic B-WR yellow	yellow	1 piece
9731330	pronamic B-WR red	red	1 piece
9731530	pronamic B-WR blue	blue	1 piece

uvex pronamic B-S-WR

Article-Nr.	Designation	Color	Packaging unit
9731031	pronamic B-S-WR white	white	1 piece
9731131	pronamic B-S-WR yellow	yellow	1 piece
9731331	pronamic B-S-WR red	red	1 piece
9731531	pronamic B-S-WR blue	blue	1 piece

uvex pronamic S-KR

Article-Nr.	Designation	Color	Packaging unit
9731033	pronamic S-KR white	white	1 piece
9731133	pronamic S-KR yellow	yellow	1 piece
9731333	pronamic S-KR red	red	1 piece
9731533	pronamic S-KR blue	blue	1 piece

uvex pronamic E-WR

Article-Nr.	Designation	Color	Packaging unit
9730030	pronamic E-WR white	white	1 piece
9730130	pronamic E-WR yellow	yellow	1 piece
9730330	pronamic E-WR red	red	1 piece
9730530	pronamic E-WR blue	blue	1 piece

uvex pronamic E-S-WR

Article-Nr.	Designation	Color	Packaging unit
9730031	pronamic E-S-WR white	white	1 piece
9730131	pronamic E-S-WR yellow	yellow	1 piece
9730331	pronamic E-S-WR red	red	1 piece
9730531	pronamic E-S-WR blue	blue	1 piece

Accessories:

Article-Nr.	Designation	Packaging unit
9790021	Chin strap EN 397	1 piece
9790031	Elastic chin strap	1 piece
9790035	2-Point chin strap	1 piece
9790022	Chinstrap-/ goggle-clip	1 piece
9772002	IES-clip with for pheos-spectable	1 piece
9790084	IES-clip with for pheos-s-spectable	1 piece
9790085	IES-clip with for i-works-spectable	1 piece
	All uvex hearing protection solutions with helmet connection	
	Visors which are specified for the pronamic alpine	
	All helmet lamps from the uvex range	

Spare parts:

Article-Nr.	Designation	Packaging unit
9790310	Suspension system	1 piece
9790311	Sweatband	10 piece

UVEX ARBEITSSCHUTZ GMBH
Wuerzburger Str. 181-189
90766 Fuerth, GERMANY
T: +49 (0) 911 97 36 0
E: serviceteam@uvex.de
I: uvex-safety.de