RevNo	Revision note	Date	Signature	Checked
1	Initial Draft Version	20251119	Leo	
2				
3				





NOTES:

1. DISPLAY TYPE:6.01″,1080*2160
2. DISPLAY MODE: AM OLED
3. LCM (White 9 AVG 1/9) :
   Brightness: 600/m^2 (TYP)
   Uniformity:80%(MIN)
4. OPERATING TEMP: -20° C TO 70° C,STORAGE TEMP: -30° C TO 80° C
5. * Critical Parameter,( ) ref Parameter,[ ] cpk Parameter
   Unspecified Tolerances:±0.20mm
   Modification mark:
6. REQUIREMENTS ENVIRONMENTAL PROTECTION: RoHS

Limits Unless Otherwise Noted					Signature	Date	Material		4D SYSTEMS PTY LTD		
Tolerance Grade				Design			Unit	mm			
Grade	◎			Drawing							
0 - 150	±0.10	±0.15	±0.20	Check			Scale	1:1	Customer NO.		
150+	±0.20	±0.25	±0.30	Approval					Drawing NO.	4DHDMI-060-1080-2160-C	
Angle	±0.50°	±0.80°		Customer confirm			Date	20251119	Projection	Ver.	1.0