Product datasheet
Characteristics

NSYTRAL22

NSYTR plug-in bridge 2 ways for 2.5mm² terminals



Main

Range	Linergy
Product name	Linergy TR
Product or component type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block TRH IDC terminal block TRP push-in terminal block TRR spring terminal - passthrough terminal block TRR spring terminal - protective earth terminal block TRR spring terminal - blade disconnect terminal block TRR spring terminal - removable carrier disconnect terminal block
Number of ways	2 ways

Complementary

Cable cross section	2.5 mm²
Number of terminals	2 3 4
Number of measurement input	1 4 2 3 6
Quantity per set	Set of 50
Product weight	1.7 g
Colour	Red

Environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity
REACh	Reference contains SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.