ENGLISH

Datasheet

Type E - French 4 Gang DC Power Socket 2.5m Cable, 16A, 230 V ac

RS Stock 755-3999

Specification:

- Socket type : NFC61-314 (socket 2)
- Socket quantity : 4
- Cable specification : Cable HO5VVF 3G 1.5 with DIN 49441 16 Plug, 2.5M
- Rating voltage : 230VAC 50/60Hz
- Max. Power : 16A, 3680W
- Product size : LxWxH = 482.6 x 44.4 x 46.5 mm
- Control Function : lightning protection with single power indicator
- Vertical and horizontal mounting
- RoHS

Series Connection: Several combinations of positive and negative power rails, such as ± 5V, ±12V etc., may be obtained, at currents up to the rated limit, by connecting the positive terminal of one output to the negative terminal of the other output with the junction being at ‘0V’.
Parallel Connection: Current may be increased by connecting the two outputs in parallel (positive to positive and negative to negative).

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.