

►► 1-series 1/4" (6.35mm) drive bit set

AME.B Box set of 9 bits + bit holder

- "Torsion" bits for Phillips® and Pozidriv® heads.
- Spring-clip bit holder EF.6P1.
- Compact box 115 x 52 x 21 mm.



AME.B	mm	no.	no.	mm	no.	n°	ΔΔ g
AME.B3	0,6 x 4,5 - 1 x 5,5 - 1,2 x 6,5	1 - 2 - 3	1 - 2 - 3				100
AME.B4	0,6 x 4,5 - 1 x 5,5		1 - 2	2,5 - 3 - 4 - 5 - 6			100
AME.B5	0,6 x 4,5 - 1 x 5,5	1 - 2			10 - 15 - 20 - 25 - 30		103
AME.B6					8 - 9	10 - 15 - 20 - 25 - 27 - 30 - 40	125

POCKET 6 Folding bit driver + bit sets

- 6 drivers in 1.
- Bits stored in handle.
- Magnetic bit holder. Ø 1/4".
- Closes to a compact size.
- EFPZ includes bits for slotted and Pozidriv® heads.
- EH includes hexagon bits.

EF	mm	no.	mm	ΔΔ g
EFPZ	4,5 - 6,5 - 8	1 - 2 - 3		200
EH			2,5 - 3 - 4 - 5 - 6 - 7	200



"Fitters" set

AME.JE1

- Comprising 16 tools :
- x15 1/4" drive bits and 1 hinged bit holder.
- ● Torsion type for slotted heads 0.5 x 4 - 0.6 x 4.5 - 0.8 x 5.5 - 1.2 x 6.5 mm
- ⊕ High Perf' type for Phillips® heads PH0 - 1 - 2 - 3
- ⊕ High Perf' type for Pozidriv® heads PZ1 - 2.
- ○ : For hexagon heads 2 - 2.5 - 3 - 4 - 5 mm.
- Bit holder with hinged handle AMH.142.
- Supplied in a case 125 x 95 x 28 mm.
- ΔΔ : 250 g.



"Motor mechanics" set

AME.JE2

- Comprising 16 tools :
- x15 1/4" drive bits and 1 hinged bit holder.
- ● High Perf' type for slotted heads 0.5 x 4 - 0.6 x 4.5 - 0.8 x 5.5 - 1.2 x 6.5 mm,
- ⊕ ⊕ : High Perf' type for Pozidriv® heads PZ.0 - 1 - 2
- ○ : For hexagon heads 2.5 - 3 - 4 - 5 mm.
- ⊕ : For Torx® heads no. T 10 - 20 - 25 - 30
- Bit holder with hinged handle AMH.142.
- Supplied in a case 125 x 95 x 28 mm.
- ΔΔ : 250 g.

