SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 12 (4) A 250 V AC

single-pole	Switch with OFF position in the center (SPDT - Center OFF)	1808.1101	1808.1102	1808.1103	1808.1112	1808.1113	1808.1202	1808.1302	1808.2102	1808.2302	1808.2704	1808.6102	1808.6103	1808.6202	1808.6302	1808.6303	1808.1152
Voltage lamp in V																	
Actuator color / printing																	
Housing color																	
12 (4) A 250 V AC 1E4																	
10 (4) A 250 V AC 1E4																	
8 (8) A 250 V AC 5E4																	
6 (4) A 250 V AC 5E4																	
6 (2) A 250 V AC 1E4		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
4 (3) A 250 V AC 6E3																	
4 (2) A 250 V AC 1E4																	
30 mA 12 V 5E4																	
30 mA 12 V DC 5E4																	●
15 A 250 V AC 1 1/2 HP																	
15 A 125 V AC 3/4 HP																	
10 A 250 V AC 1/2 HP																	
10 A 125 V AC 1/3 HP																	
6 A 250 V AC 1/2 HP																	
6 A 125 V AC 1/4 HP																	
6 A 125 - 250 V AC 1/8 HP		●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
6 A 125 V AC 1/10 HP																	
4 A 250 V AC 1/10 HP																	
Connection type																	
Connection description		4.8	4.8	4.8	4.8	4.8	4.8	4.8									4.8
Inrush current in A (capacitive)																	
Contact distance in mm		<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	<3
Contact material		Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Au
EN 60335 cap. 30 conform "G"					●											●	
Miscellaneous							momentary function one side	momentary function both sides	PCB lined	PCB lined momentary function both sides	installation depth 29.6			momentary function one side	momentary function both sides	momentary function both sides	
Stock version		●	●	●			●	●	●	●		●		●	●		