

Indicator light, 16 mm, round, plastic, clear, smooth, for inscription with insert caps



Figure similar

|  |                      |
|--|----------------------|
| product brand name   | SIRIUS               |
| product designation  | Indicator lights     |
| design of the product  | Single device round  |
| product type designation                                       | 3SB2                 |
| <b>Enclosure</b>   |                      |
| number of command points                                       | 0                    |
| <b>Actuator</b>  |                      |
| design of the actuating element                                | indicator light      |
| product extension optional light source                        | No                   |
| color of the actuating element                                 | clear                |
| material of the actuating element                              | plastic              |
| shape of the actuating element                                 | Smooth lens          |
| outer diameter of the actuating element                        | 19 mm                |
| type of unlocking device                                       | without              |
| number of switching positions                                  | 0                    |
| <b>Front ring</b>  |                      |
| product component front ring                                   | No                   |
| <b>Holder</b>  |                      |
| material of the holder   | Plastic              |
| <b>General technical data</b>                                  |                      |
| product function   |                      |
| • EMERGENCY OFF function                                       | No                   |
| • EMERGENCY STOP function                                      | No                   |
| protection class IP  | IP65                 |
| vibration resistance according to IEC 60068-2-6                | 20 ... 200 Hz: 5g    |
| reference code according to IEC 81346-2                        | P                    |
| Substance Prohibitance (Date)                                  | 07/01/2006           |
| Weight   | 0.01 kg              |
| <b>Connections/ Terminals</b>                                  |                      |
| tightening torque of the screws in the bracket maximum         | 0.4 N·m              |
| <b>Ambient conditions</b>                                      |                      |
| ambient temperature  |                      |
| • during operation   | -25 ... +70 °C       |
| • during storage   | -40 ... +80 °C       |
| environmental category during operation according to IEC 60721 | 3K6                  |
| <b>Installation/ mounting/ dimensions</b>                      |                      |
| fastening method   | front plate mounting |
| shape of the installation opening                              | round                |

|                    |       |
|--------------------|-------|
| mounting diameter  | 16 mm |
| mounting height    | 9 mm  |
| installation width | 19 mm |
| installation depth | 50 mm |

#### Approvals Certificates

|                          |                   |
|--------------------------|-------------------|
| General Product Approval | Test Certificates |
|--------------------------|-------------------|



[Miscellaneous](#)

[Special Test Certificate](#)

|                   |       |             |
|-------------------|-------|-------------|
| Test Certificates | other | Environment |
|-------------------|-------|-------------|

[Type Test Certificates/Test Report](#)



[Confirmation](#)

[Environmental Confirmations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2001-6CH06>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2001-6CH06>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2001-6CH06>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SB2001-6CH06&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2001-6CH06&lang=en)

last modified:

4/2/2025