

EMG738

Cut level C / A3 cut resistant glove with nitrile sandy coating

A soft and comfortable medium cut resistant glove with sandy nitrile coating. Ideal for handling sharp parts in dry, oily or greasy conditions.

Features

- ▲ Durable sandy nitrile palm coating ensures good abrasion protection and excellent grip in wet and oily environments
- ▲ Contact heat protection up to 100°C / 212°F for a short period (15 sec max)
- ▲ Reinforced thumb crotch enhances durability
- ▲ Breathable back of hand to reduce perspiration
- ▲ Seamless knit prevents irritation
- ▲ Elasticated wrist provides a secure fit



Certifications



Suitable industries & applications

Industries

- ▲ Aerospace
- ▲ Automotive

- ▲ Construction

Applications

- ▲ Component and Product Assembly
- ▲ General Goods Handling
- ▲ Woodwork and Fabrication
- ▲ General Maintenance

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

EMG738

Cut level C / A3 cut resistant glove with nitrile sandy coating

Product information

Materials	Liner:	13 Gauge Glass Fibre, HPPE, Nylon
	Coating:	Sandy Nitrile
Colour	Grey / Black	
Length	220mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

XS	EMG00738FB	Items per Pack 10 x Pairs
S	EMG00738FD	
M	EMG00738FF	Items per Case 120 x Pairs
L	EMG00738FH	
XL	EMG00738FJ	
XXL	EMG00738FL	
XXXL	EMG00738FN	

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.