



Part Number : [2002220300](#)
Product Description : Insertion/Extraction Tool for MultiCat Mid-Power Crimp Terminals, 28-20 AWG
Series Number : 207121
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[2002220300-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Insertion/Extraction Tool for MultiCat Mid-Power Crimp Terminals, 28-20 AWG
Comments	See Tooling Specification (PDF) Above
Function	Insertion/Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	MultiCat
Tool Type	Extraction Hand Tool, Insertion Hand Tool
UPC	193264021659
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where

	Molex Tooling is modified.
--	----------------------------

Physical

Net Weight	226.000/g
------------	-----------

Applicable Parts

Description	Part Number
MultiCat Mid-Power Crimp Terminal, Male, 0.20µm Gold Plating, 24-20 AWG	<u>2029351000</u>
MultiCat Mid-Power Crimp Terminal, Male, 0.20µm Gold Plating, 28-26 AWG	<u>2029352000</u>
MultiCat Mid-Power Crimp Terminal, Male, 1.30µm Gold Plating, 24-20 AWG	<u>2029353000</u>
MultiCat Mid-Power Crimp Terminal, Male, 1.30µm Gold Plating, 28-26 AWG	<u>2029354000</u>
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 24-20 AWG, with Sleeve	<u>2029360100</u>
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 28-26 AWG, with Sleeve	<u>2029360200</u>
MultiCat Mid-Power Crimp Terminal, Female, 0.20µm Gold Plating, 24-20 AWG, without Sleeve	<u>2029361000</u>
MultiCat Mid-Power Crimp Terminal, Female, 0.20µm Gold Plating, 28-26 AWG, without Sleeve	<u>2029362000</u>
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 24-20 AWG, without Sleeve	<u>2029363000</u>
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 28-26 AWG, without Sleeve	<u>2029364000</u>