40B – Slim Wrenches





Description:

- **12-Point OGV® Profile** – Maximising the contact surface with the nut.
- Matte finish
- **Ring-end angled at 15°**– Prevents fingers from coming into contact with nearby surfaces, offering safe and comfortable use.
- **Open-end angled at 15°** – Reduced recovery angle for increased accessibility.
- **ISO 691, ISO 1711-1, ISO 3318, ISO 7738, DIN 3113**

	A (mm)	B (mm)	B1 (mm)	C (mm)	C1 (mm)	L (mm)
40B.5	5	14.7	9	3.4	4	93
40B.5.5	5.5	14.7	9	3.4	4	93
40B.6	6	16.2	10.4	3.7	4.5	100
40B.7	7	18.2	11.7	3.7	5	110
40B.8	8	20.2	13.2	4	5	120
40B.9	9	22.2	14.6	4	6	130
40B.10	10	23.7	16	4	6.5	140
40B.11	11	25.7	17	4.7	6.5	150
40B.12	12	27.5	19	4.8	7	160
40B.13	13	28.7	20.6	5.5	7.5	170
40B.14	14	31.7	22	5.6	8	180
40B.15	15	34	23.4	5.7	8.5	190
40B.16	16	36	24.8	5.8	9	200
40B.17	17	38.5	26.2	6.3	9.5	210
40B.18	18	39	27.6	6.8	10	220
40B.19	19	42.2	29	7.1	10.4	230
40B.20	20	42.7	30.2	7.2	10.9	240
40B.21	21	45.5	31.7	7.5	11.4	250
40B.22	22	48.7	33	8	11.9	260
40B.23	23	48.7	33	8	11.9	260
40B.24	24	50.7	35	8	12.9	280
40B.25	25	52.7	38	8	13.4	295
40B.26	26	52.7	38	8	13.4	295
40B.27	27	56.2	40	8.9	14.4	310
40B.28	28	60.2	44.6	9	15.9	340
40B.29	29	60.2	44.6	9	15.9	340

40B.30	30	60.2	44.6	9	15.9	340
40B.32	32	64.7	47.3	10.6	16	360
40B.34	34	68.7	49.3	11.5	17.2	380
40B.36	36	73	53.4	13	18.2	410
40B.38	38	76	56.5	14.5	19	430
40B.41	41	83.5	61.5	15.5	20	460