Lighting **excellence**

@4liteuk @4liteuk

@4lite @4liteuk

T8 LED Tube CCT

Application	Industrial

T8 LED Tube CCT 1200mm

Code: 4L3/3001



Product Features

- Energy-efficient T8 LED glass tube
- Adjustable wattage, allowing selection between high or low output
- Easy to install and the perfect replacement for traditional fluorescent T8 tubes
- Instant light output
- Suitable for residential and commercial applications
- 3 CCT Selectable between 3000K, 4000K & 6500K
- High efficacy up to140 lm/w
- 5 year warranty

Technical Information	
Wattage	9W / 18W
Lumens Delivered	1300lm / 2500lm (4000K)
Lm/W	140lm/w / 150lm/w
Beam Angle	360
CRI	80
CCT	3000/4000K/6500
Input	220-240V
Operating Temp	-20°C to 45°C
SDCM	6
Product Weight without Packaging	0.197 kg

Technical Information	
Light Source	T8
IP Rating	IP20
Class Protection	2
Internal / External	Internal
Lumen Depreciation	L70 B50 25,000h
Warranty (Years)	5
CE Mark	Yes
Diameter	28 mm