Date: 23/01/2024

A43.30.080 0 °C ... 60 °C L1=40 x 9 mm alu CL.2

Bimetallic thermometer, for heating technology A43

Item number:	14141147
Quantity:	1 pcs.
Order code:	A4330080A-C1C-040ECFBB-1ZZZZZ1-KSK2ZZZ
Overview:	A43.30.080 0 °C ... 60 °C L1=40 x 9 mm alu CL.2 Case material: Plastic, black; pointer: plastic, black Window: acrylic, (SAN) Thermowell: detachable, with retainer screw; Brass Process connection [E, d6]: G1/2B *WIKA* Dial color, 1-colored
Details:	Bimetallic thermometer, for heating technology A43 Model: A43 Design: standard, plastic case Nominal size [NG, d1]: 80 mm Case material: Plastic, black; Unit: °C Scale range: 0 °C ... 60 °C Insertion length [L1]: 40 mm Stem diameter [d5]: 9 mm Stem material: aluminum Thermowell: detachable, with retainer screw; Thermowell material: Brass Process connection [E, d6]: G1/2B Manufacturer logo: *WIKA* Dial printed (Number of colors): Dial color, 1-colored pointer model: plastic, black Window: acrylic, (SAN) Accuracy class: class 2 per EN 13190

© 2024 - WIKA Instruments s.a.r.l.