


LED Tube Fixture T8 1x 1500 G13 IP20

Article number: 145098

BAI Surface-mounted Fixture for LED Tube 1xT8 1500mm G13 230V/AC (lamp not included) IP20 55x80x1530mm

This fixture is a housing for a LED T8 AC 220-240V tube with G13 fitting. The fixture is easy to install to the ceiling. The tube is placed in the fixture with a simple twisting movement. This fixture is supplied without LED tube. You can choose the LED tube that suits you best. Note: This fixture is only suitable for LED tubes, not for fluorescent tubes!







General ETIM properties

ETIM group	Luminaires
ETIM class	Batten luminaire
Name	LED Tube Fixture T8 1x 1500 G13 IP20
Brand	Bailey
Productseries	Relamp T8
Producttype	LED T8 FIXTURE 1500

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

ETIM specifications

Length [mm]	15350
Lamp type	LED exchangeable
With light source	No
Suitable for number of light sources	1
Lamp holder	G13
Suitable for lamp power [W]	58 - 58
Material	Steel
Housing colour	White
Voltage type	AC
Nominal voltage [V]	220 - 240
Type of control gear	Not required
With control gear	No
Exchangeable control gear	No
Dimming 0-10 V	No
Dimming 1-10 V	No
Dimming DALI	No
Dimming DMX	No
Dimming DSI	No
Dimming potentiometer (integrated)	No
Dimming LineSwitch	No
Dimming manufacturer's proprietary system	No
Dimming mains voltage modulation	No
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming programmable	No
Dimming RF	No
Dimming Sine Wave Reduction	No
Dimming Touch and Dim	No
Dimming Zigbee	No
Dimming with push-button	No
Light distributor	None
Degree of protection (IP)	IP20
Degree of protection (NEMA)	Other
Protection class according to IEC 61140	I
Luminaire with limited surface temperature, sign "D“ according to EN 60598-2-24	No
Covering of the luminaire with thermally insulating material possible	No
Suitable for emergency lighting	No
With switch	No
With movement sensor	No
Max. system power [W]	58
Colour of light adjustable	No

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

Luminous flux adjustable	No
Beam angle adjustable	No
Width [mm]	55
Height/depth [mm]	80
Type of wiring	Ending
Number of poles	3
Conductor cross section [mm²]	0.5
Connection type	Other
Electrical connection with connector system	Yes
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
With lamp protection basket	No
Operation by Bluetooth	No
Compatible with Casambi	No
Dimmable	No
Dimming DALI-2	No
Containing product according to 2019/2020/EU	No
Impact strength	IK02
Emergency power supply system	None
Emergency function monitoring system	None
With presence detector	No
With light sensor	No
Connectable conductor cross section [mm²]	0.5 - 2.5

Alternative articles



146962

Relamp LED T8 Tube Batten 1x 1500 G13 IP65 IK10

Complementary articles

All rights reserved. We reserve the right to change designs and technical specifications of our products.s



145868

LED Ecoplus T8 Switch 1500 G13 22W (58W) 2420lm 830-865 EM+AC



145760

LED Ecobasic T8 1500 G13 24W (58W) 2640lm 865 EM+AC

Successor

147155

Relamp LED T8 Tube Fixture 1x 1500 G13 IP20

All rights reserved. We reserve the right to change designs and technical specifications of our products.s