

CE-certified, PVC gloves combining chemical and mechanical resistance with superior grip (260mm/10" length)

- **Enhanced durability:** Fully-coated with PVC, EDGE[®] 14-662 safety gloves ensure greater flexibility and comfort, while protecting hands against chemical, mechanical and biological hazards, in addition to delivering heat and abrasion resistance, and are thereby ideal for workers exposed to oil, grease, acid, caustics and alcohol
- **Optimized protection:** These durable work gloves feature a rough, non-slip finish on the palm, fingers and back of hand, enabling them to afford an outstanding grip in wet and oily conditions as they guard against abrasion
- **Reduced risks:** CE-certified, EDGE[®] 14-662 industrial gloves meet European safety, health and environmental protection requirements and are among the most cost-effective PVC work gloves available

Industries

- Oil and gas
- Chemical
- Manufacturing
- Infrastructure Maintenance
- Utilities

Applications

- Chemical processing and preparation
- Handling dry, wet or oily large objects
- Maintenance of plant and machines



Key Features

- **PVC coating:** Protective gloves with optimized flexibility and comfort
- **Non-slip finish:** Gloves with grip enhanced by rough, non-slip surface
- **CE-certified:** For assured safety and high-quality work gloves



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
EDGE® 14-662	Coating Material: PVC	8, 9, 10, 11	260 mm / 10 Inches	Blue	12 pairs/bag, 6 bags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.