AGLED/3M

Features

Ultra-slim profile LED polycarbonate bulkhead.

Supplied with self-adhesive legend.

20mm side, end and rear cable entries.

Hinged screwless gear tray for ease of installation.

Viewing distance 18 metres.

General Information

Lamp Type	LED
Colour / Finish	White
IP Rating	IP65
Class Protection	1
Internal / External	Internal/External
Surface / Recessed / Suspended	Surface
Warranty (Years)	3
CE Mark	Yes
Width (mm)	352
Height (mm)	110
Depth (mm)	64
Accessories	AGLED/KIT, ASBP/2

Technical Information

Wattage	3W
Lumens Delivered	144lm (Emergency), 180lm (Standard)
CCT	6500K
Input	230V
Hertz	50/60Hz
Operating Temp	0C° to 40C°

Datasheet generated from https://onetimepim.com last updated Monday, June 28, 2021 11:59:38 AM

55
110
352