
## 1559484 DSM-T-10-90-P Semi-rotary drive - Series: All



# 1559484 DSM-T-10-90-P Semi-rotary drive - Series: All

| Pos. | Part no. | Type | Note | Qty. | Unit |
|---|---|---|---|---|---|
| A | 384303 | DSM- 10-...-P<br>Set of wearing parts | Spare parts: 5, 10, 11<br>Replacing the wearing parts | 2 | PC |
| 1 | 257139 | A-2X2X12-1.0503+C<br>Feather key DIN6885 | | 1 | PC |
| 2 | 1515179 | DSM-T-10<br>Shaft | | 1 | PC |
| 3 | 257138 | D616-688-2RS<br>Deep groove ball bearing | | 2 | PC |
| 4 | | DSM-10:LE<br>Housing | Not available<br>Grease using during assembly. See position 11 | 1 | PC |
| 5 | | DSM- 10-<br>Vane | Not available separately, see position A<br>Grease using during assembly. See position 11 | 2 | PC |
| 6 | | DSM-T-10<br>Housing | Not available<br>Grease using during assembly. See position 11 | 1 | PC |
| 7 | | DSM-T-10:RECHTS<br>Housing | Not available<br>Grease using during assembly. See position 11 | 1 | PC |
| 8 | 208623 | DIN 6799-5<br>Retaining washer | | 1 | PC |
| 9 | 352090 | ISO 4762-M3X35-8.8<br>Socket head screw | Tightening torque 1.2 Nm / 0.9 lbf ft | 4 | PC |
| 10 | | DSM- 10- 90<br>Chamber seal | Not available separately, see position A<br>Grease using during assembly. See position 11 | 2 | PC |
| 11 | 684474 | LUB-KC1 SILIKONFREI 20ML<br>Lubricating grease | | 1 | PC |