Product data sheet
Characteristics

DZ5CA003
single conductor insulated markable cable end - medium - 0.34 mm² - green



Main

Range of product	Cable ends
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	0.34 mm²

Complementary

Cable end type	Single conductor
Additional information	With integrated marker tag holder
Colour	Green
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	24
Bezel size	Ø 2.2 mm
Tube diameter	1.2 mm
Length	13 mm
CAD overall width	2 mm
CAD overall height	2 mm
CAD overall depth	30 mm
Product weight	0.14 kg

Environment

Ambient air temperature for operation	-20...105 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.