
Part Number : 1731110018
Product Description : FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 5, Straight or 90° Angle Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws, Individual Packing
Series Number : 173111
Status : Active
Product Category : D-Sub Backshells
Engineering Number : FPHGR-5AE



Documents & Resources

Drawings
1731110018_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	173111
Description	FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 5, Straight or 90° Angle Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws, Individual Packing
Magnetic	Yes
Product Name	FCT Products
Type	Plastic
UPC	889056319423

Electrical

Shield Type	Shielded Plastic
Shielded	Yes

Physical

Cable Diameter	14.00mm
Material - Backshell	PC+ABS
Material - Screw	Steel
Mounting Style	Locking Screw
Net Weight	30.600/g
Orientation	Straight or 90° Angle
Packaging Type	Bag
Plating - Backshell	Nickel
Temperature Range - Operating	-35° to +95°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 5