Date: 23/01/2024

A48.10.080 0...80°C L1=100x9mm copper alloy CL.2

Bimetallic thermometer TYP48-50

Item number:	13136870	
Quantity:	1 pcs.	
Order code:	A48.10.080-G-C1D-100DMZZFV-1ZZZZZZZBK-ZZZ	2BZTM4801
Overview:	A48.10.080 0...80°C L1=100x9mm copper alloy CL.2 Case material: aluminium Pointer: plastic, black Window: acrylic, (SAN) galvanised steel flange, adjustable on stem, diameter of pitch circle 51mm/D61mm Dial background: white *WIKA* Data sheet: TM48.01	
Details:	Bimetallic thermometer TYP48-50 Model: A48 For air conditioning and ventilation technology Design: standard, aluminium case Nominal size [NG, d1]: 80 mm Case material: aluminium Unit: °C Scale range: 0 °C ... 80 °C Insertion length L1: 100 mm Stem diameter: 9 mm Stem material: copper alloy Process connection: galvanised steel flange, adjustable on stem, diameter of pitch circle 51mm/D61mm Manufacturer logo: *WIKA* Pointer: plastic, black Window: acrylic, (SAN) Accuracy class: class 2 per EN 13190 Dial background: White Data sheet: TM48.01	

© 2024 - WIKA Instruments s.a.r.l.