PRODUCT-DETAILS

XT4H 160 Ekip I In=160A 4p F F

XT4H 160 Ekip I In=160A 4p F F

General Information

Extended Product Type	XT4H 160 Ekip I In=160A 4p F F
Product ID	1SDA068539R1
EAN	8015644024451
Catalog Description	XT4H 160 Ekip I In=160A 4p F F
Long Description	C.BREAKER TMAX XT4H 160 FIXED FOUR-POLE WITH FRONT TERMINALS AND SOLID-STATE RELEASE IN AC EKIP-I R 160 A

Ordering

EAN	8015644024451
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	140 mm
Product Net Height	160 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	3.05 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	145 mm
Package Level 1 Height	210 mm
Package Level 1 Depth / Length	168 mm
Package Level 1 Gross Weight	3.5 kg
Package Level 1 EAN	8015644024451

Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Additional Information

Circuit Breaker Type to be Associated	Power Distribution
Current Type	AC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	Nr. Operations 240 cycles per hour Nr. Operations 25000 cycle
Number of Poles	4
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current (I_n)	160 A
Rated Frequency (f)	50 / 60 Hz
Rated Voltage (U_r)	690 V
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(220 V AC) 100 kA (230 V AC) 100 kA (240 V AC) 100 kA (380 V AC) 70 kA (415 V AC) 70 kA (440 V AC) 65 kA (500 V AC) 50 kA (525 V AC) 45 kA (690 V AC) 15 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(220 V AC) 100 kA (230 V AC) 100 kA (240 V AC) 100 kA (380 V AC) 70 kA (415 V AC) 70 kA (440 V AC) 65 kA (500 V AC) 50 kA (525 V AC) 45 kA (690 V AC) 15 kA
Rated Uninterrupted Current (I_u)	160 A
Release	Ekip I
Release Type	EL
Short-Circuit	H

Performance Level	
Standards	IEC
Sub-type	XT4
Terminal Connection Type	Fixed Circuit-Breakers
Version	F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210100D0206 1SDC210099D0206
Declaration of Conformity - CE	9AKK106713A5529
Environmental Information	1SDL000190R0001
GL Certificate	1SDL000163R0095
Instructions and Manuals	1SDH000722R0001
LR Certificate	1SDL000163R0100

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39120000
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT