Lighting **excellence**

@4liteuk @4liteuk

@4lite @4liteuk

Valde

Application	Industrial

Valde IP65 Non Corrosive Multi Wattage 1200mm Emergency
Code: 4L3/1140/EM







Product Features

- 3 CCT colour selectable feature
- Hybrid body size
- Multiple cable entry / conduit entry points
- Adjustable sliding fixing bracket
- Multi wattage
- Available in 1200mm / 1500mm / 1800mm lengths
- Detachable terminal block with multiple positions adjacent to all cable entry points
- Also available as Emergency and Microwave options

Technical Information	
Wattage	22W / 28W / 34W / 40W
Lumens Delivered	3080lm - 5600lm (4000K)
Lm/W	140lm/W
Beam Angle	120
CRI	80
CCT	3000K/4000K/6500K
Input	220-240V
Operating Temp	0°C - 40°C
SDCM	6
UGR	25

Technical Information	
Light Source	LED
Colour / Finish	Grey
IP Rating	IP65
Class Protection	1
Internal / External	Internal / External
Mounting Option	Surface, Suspended
Lumen Depreciation	L70 50,000h
Warranty (Years)	4
CE Mark	Yes
Height	75 mm