COMPOSITE RATCHET WRENCH 1/2"

RC590

SAM Outillage
10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France
RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬
https://www.sam-outillage.com/

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:01

DESCRIPTION

COMPOSITE RATCHET WRENCH 1/2"

Two good reasons for buying it:- Perfect ergonomics for great great working comfort.- A profiled spindle guided by needle bearings backed up be an epicyclic gear train speed reducer for reliability and precision.

COMPACT This 1/2" ratchet wrench - the thinnest on the market to date - is designed for intense use. COMPLETE It has a high tightening torque (14-70 Nm) for great tightening quality. ESSENTIAL Heat treatment for the frame/ratchet for greater strength, ensuring that this wrench provides optimum tightening. It has the best equipment: composite material for comfort and protection against the cold, profiled head for access to restricted spaces, precision-engineered bearings for reliability. Ergonomic sheathing with area for positioning the thumb and a stop for the index finger enabling an excellent grip. Swivel rear exhaust on silencer. Variable speed control and 360° coupling. Heat treatment for the frame/ratchet for greater strength.

STANDARDS / DIRECTIVES

ISO 11148-6, ISO 15744, ISO 28927-2

SPECIFIC DATA

Designation	COMPOSITE RATCHET WRENCH 1/2"
Sales reference	RC590
L (mm)	315
Weight (g)	1350
l (mm)	21
H (mm)	30
drive square	1/2"
Rotation speed (rpm)	150
Vibration (m/s²)	2,6
Noise level (dBa)	79
C mm	6,2
C min mm	1/4"
C mm	70
Maximum input torque Nm	
Guarantee	M2 | SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee
Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

>> Find out more