Technical data sheet

Article number:
924-00471 BL2.5/500

Product Group	Bootlace Ferrule
Product Family	Nylon Insulated Bootlace Terminal
Material	Copper (CU), Polyamide 6.6 (PA66)
Colour	Grey (GY)

Application Range	Low Voltage
Conductor Size (mm²)	2.5 mm²
Diameter (D)	4.2 mm
Halogen-free	Yes
Length (L)	14 mm
Length (L2)	6 mm
Length (L3)	8 mm
Max Voltage	600 V
Operating Temperature	-30 °C to +105 °C
Package Content packed in	bag
REACh Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	2.2 mm
ROHS compliant	Yes

HF RoHS

created on 11. May 2026, 12:37 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.