PRODUCT-DETAILS

RH9711

INS NYL RING TERM, 1AN, 1/4, CLEAR

General Information

Extended Product Type	RH9711
Product ID	7TAI029870R0085
EAN	5414363160236
Catalog Description	INS NYL RING TERM, 1AN, 1/4, CLEAR
Long Description	Nylon Insulated Large Ring Terminal, Length 2.14 Inches, Width .77 Inches, Maximum Insulation .500, Bolt Hole 1/4 Inch, Wire Range 1AN, Color White, Copper, Tin Plated, 50 Pack

Ordering

EAN	5414363160236
UPC	786210821221

Dimensions

Product Net Length	0, mm

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	4.5 in 114 mm
Package Level 1 Height	3 in

	76 mm
Package Level 1 Depth / Length	5 in 127 mm
Package Level 2 Units	500 piece
Package Level 2 Width	10.7 in 272 mm
Package Level 2 Height	3.5 in 89 mm
Package Level 2 Depth / Length	23.9 in 607 mm

Additional Information

Brand / Label	Sta-Kon
Color	White
Effective Date	19680527
Material	Copper
Number of Batteries	0
Product Name	ELECTRICAL TERMINAL
Product Type	Nylon Insulated Ring Terminal
Special Functions	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standards	UL E9809
Voltage Rating	600 V
Wire Size	1AN

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	RH9711
Instructions and Manuals	RH9711

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors