HellermannTyton

Technical data sheet

Article number:
924-00543 2S6

Product Group	Spade/Forks Terminals
Product Family	Single Grip Pre-Insulated
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Blue (BU)

Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm²
Diameter (D)	4.7 mm
for Hole Ø (FH)	6.4 mm
Length (L)	23 mm
Length (L2)	10.7 mm
Length (L3)	12.3 mm
Max Current	27 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACh Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	10.7 mm

RoHS

created on 11. May 2026, 12:30 pm

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.