



jalas® EXALTER 9995

EN ISO 20345:2022 S3S, HRO, FO, SC ASTM F2413-18 M/I/C SD 35 PR

Learn more

NEW SUSTAINABLE GENERATION

Exalter's new generation is upgraded with several recycled and bio-based materials without compromising the superior combination of durability, comfort, and lightness that users have relied on for years. Bio-based microfiber water repellent upper keeps the feet dry. BOA® Fit System (from recycled material) on the side eliminates pressure points. Aluminum toe cap and recycled metal-free nail protection insert with high-grip Vibram® recycled nitrile rubber outsole.

CHARACTERISTICS

- Excellent shock absorption
- Excellent grip
- Perfect fit
- Extra comfortable
- High level of protection

FUNCTIONS

- Oil-resistant outsole
- Anti-static properties
- Ventilating insole
- BOA® Fit System
- Double shock absorption zones
- Heat-resistant outsole
- Water repellent
- Polstered shaft edge
- Ergonomically shaped
- Conforms with IEC 61340-5-1 (ESD)
- Quick-tie
- Stabilizator
- Soft
- Specially designed details
- Free from animal-derived materials

BOA DIALED IN. PRECISION FIT. Xrd PROTECTION EcoFlex Vibram

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, nail penetration, sprain injuries, antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, indoors, all-year use, warm surfaces, environments with risk for outsole penetration, dry environments, clean environments, moist environments, dirty environments

PRIMARY AREAS OF USE

Agricultural work, assembly, building and construction, carpentry, concrete work, construction, engineering, fine assembly, fishing industry work, forest work, gardening, inspection work, installation work, machine driving, machine operating, metalwork, paper industry work, repair work, sheet-metal work, transport work, warehouse work, wood industry work

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
NAIL PROTECTION MATERIAL EcoFlex Zero perforation textile
FITTING Regular
COLLECTION Exalter
UPPER MATERIAL Microfiber
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester
INSOLE JALAS 8304 FX3 Soft
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING BOA® Fit System
COLOUR Black, Orange
NET WEIGHT, (SIZE 42) 1.23 kg

COMPLIANCE

CE Cat. II

EN ISO 20345:2022
S3S, HRO, FO, SC

EAC TP TC 019:2011

ASTM F2413-18
M/I/C
SD 35 PR

FEATURES

- Aluminium toecap
- Nail protection in plasma-treated composite (PTC) textile
- Oil-resistant outsole
- Stabilizator
- Heat-resistant outsole
- Water repellent
- Ergothan Shock Absorption System
- Anti-static properties
- ESD

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
34	1½	2½	3½	9995-34	6408487554599
35	2	3½	4	9995-35	6408487554643
36	3	4	5	9995-36	6408487554698
37	4	5	6	9995-37	6408487554742
38	5	5½	6½	9995-38	6408487554797
39	6	6½	7½	9995-39	6408487554841
40	6½	7½	8½	9995-40	6408487554896
41	7	8	9	9995-41	6408487554940
42	8	9	10	9995-42	6408487554995
43	9	9½	11	9995-43	6408487555046
44	10	10½	11½	9995-44	6408487555091
45	10½	11	12½	9995-45	6408487555145
46	11	12	13	9995-46	6408487555190
47	12	13	14	9995-47	6408487555244

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.