


LED Tube Fixture T8 2x 1200 G13 IP20

Article number: 145097

BAI Surface-mounted Fixture for LED Tube 2xT8 1200mm G13 230V/AC (lamp not included) IP20 100x50x1230mm

This fixture is a housing for a LED T8 AC 220-240V tube with G13 fitting. The fixture is easy to install to the ceiling. The tube is placed in the fixture with a simple twisting movement. This fixture is supplied without LED tube. You can choose the LED tube that suits you best. Note: This fixture is only suitable for LED tubes, not for fluorescent tubes!







General ETIM properties

ETIM group	Luminaires
ETIM class	Batten luminaire
Name	LED Tube Fixture T8 2x 1200 G13 IP20
Brand	Bailey
Productseries	Relamp T8
Producttype	LED T8 FIXTURE 1200

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

ETIM specifications

Length [mm]	1230
Lamp type	LED exchangeable
With light source	No
Suitable for number of light sources	2
Lamp holder	G13
Suitable for lamp power [W]	36 - 36
Material	Steel
Housing colour	White
Voltage type	AC
Nominal voltage [V]	220 - 240
Type of control gear	Not required
With control gear	No
Exchangeable control gear	No
Dimming 0-10 V	No
Dimming 1-10 V	No
Dimming DALI	No
Dimming DMX	No
Dimming DSI	No
Dimming potentiometer (integrated)	No
Dimming LineSwitch	No
Dimming manufacturer's proprietary system	No
Dimming mains voltage modulation	No
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming programmable	No
Dimming RF	No
Dimming Sine Wave Reduction	No
Dimming Touch and Dim	No
Dimming Zigbee	No
Dimming with push-button	No
Light distributor	None
Degree of protection (IP)	IP20
Degree of protection (NEMA)	Other
Protection class according to IEC 61140	I
Luminaire with limited surface temperature, sign "D“ according to EN 60598-2-24	No
Covering of the luminaire with thermally insulating material possible	No
Suitable for emergency lighting	No
With switch	No
With movement sensor	No
Max. system power [W]	36
Colour of light adjustable	No

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

Luminous flux adjustable	No
Beam angle adjustable	No
Width [mm]	100
Height/depth [mm]	50
Type of wiring	Ending
Number of poles	3
Conductor cross section [mm²]	0.5
Connection type	Other
Electrical connection with connector system	Yes
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
With lamp protection basket	No
Operation by Bluetooth	No
Compatible with Casambi	No
Dimmable	No
Dimming DALI-2	No
Containing product according to 2019/2020/EU	No
Impact strength	IK02
Emergency power supply system	None
Emergency function monitoring system	None
With presence detector	No
With light sensor	No
Connectable conductor cross section [mm²]	0.5 - 2.5

Bailey Electric & Electronics bv | Everdenberg 21 | 4902 TT Oosterhout | nl | +31 (0)162 52 24 46 | info@bailey.nl

All rights reserved. We reserve the right to change designs and technical specifications of our products.s