

Strømimpulsbryter, 230AC, 2L, 16A, 50Hz, 1DE

Type	**Z-S230/SS**
Catalog No.	**265271**
EL-Nummer	**4133969**

Powering Business Worldwide

Data for konstruksjonsdokumentasjon iht. IEC/EN 61439

Tekniske data for konstruksjonsdokumentasjon		
Omgivelsestemperatur ved drift min.	°C	-20
Omgivelsestemperatur ved drift maks.	°C	45


Tekniske data etter ETIM 6.0

Devices for distribution board-/surface mounting (EG000062) / Latching relay (EC000188)

Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Latching relay for distribution board (ecl@ss8.1-27-14-23-06 [AFZ818012])

Function		Mechanical switch
Mounting method		DIN rail
Width in number of modular spacings		1
Built-in depth	mm	60
Number of normally open contacts		2
Number of normally closed contacts		0
Number of change-over contacts		0
Control voltage 1	V	230 - 230
Type of control voltage 1		AC
Frequency control voltage 1	Hz	50 - 50
Control voltage 2	V	0 - 0
Type of control voltage 2		AC
Frequency control voltage 2	Hz	0 - 0
Rated switch current	A	32
Supply voltage	V	250 - 250
Voltage type of supply voltage		AC
Max. incandescent lamp load	W	0
Max. load fluorescent lamp	VA	0
Max. load fluorescent lamp (Duo circuit)	VA	0
Max. load fluorescent lamp (parallel compensated)	VA	0
Max. switching current (cos phi = 0.6)	A	0
Manual operation possible		Yes

Dimensjoner



© 12/2017 by Eaton Industries GmbH