

TECHNICAL DATA

AER PARTICULATE RESPIRATOR CUP DESIGN

Model : AER-PR-20

PROGUARD®

Your Ultimate Partner In Safety®

Features & Benefit

- Adjustable noseclip.
- Comfortable headband straps.
- Soft inner layer & skin-friendly fabric.
- Protect the wearer from non-oil solid or liquid particles.

Physical Description

Filter Material	Non-woven Fabric, Cotton Fabric, & PP Meltblown Filter
Classification	FFP2 NR
Colour	White
Particle Filtration Efficiency	≥94% Filtration
Certified Standard	SIRIM PC011077 EN 149:2001+A1:2009
Packaging	20pcs/box 20 boxes/carton
Shelf-life	5 years

Care and Storage Instruction

- Recommended for one time used only, then discard the mask. Do not wash and reuse.
- Store in a well ventilated, cool and dry place, and away from direct sunlight.
- Recommended storage condition temperature between -5°C to +50°C and at less than 75% relative humidity.
- Once opened packaging, keep box close to prevent unused facemask from being contaminated from airborne particles, virus, and bacteria.

Warning

- The instructions must be carefully read before use.
- This respirator does not supply oxygen. Do not use in environment with oxygen level lower than 19.5%.
- Do not use this respirator when concentration of contaminants are immediately dangerous to life or health.

CE 2834
EN 149:2001+A1:2009



SIRIM

Certified to BS EN 149:2001+A1:2009
Certification No: PC011077



PROGUARD TECHNOLOGIES (M) SDN. BHD. (258964-U)

T +603 9021 3233 (Hunting Line) F +603 9021 3133/ 9021 2733
E proguard@proguardsafety.com
Lot 408 & 409, Jalan Sungai Tekali, 43100 Hulu Langat, Selangor, Malaysia.

SUBANG JAYA Branch :

T +603 5192 8788 F +603 5192 1788 E pgsj@proguardsafety.com
No.10, Jalan Putra Mahkota 7/6B,
47650 Putra Heights, Subang Jaya, Selangor, Malaysia.

MELAKA Branch :

T +606 335 4552 (Hunting Line) F +606 335 4557
E pgmelaka@proguardsafety.com
No.7 & 7-1, Jalan MP3, Taman Merdeka Permai, 75350 Melaka, Malaysia.

EAST COAST Branch :

T +609 567 5989/ 568 5989 F +609 568 9989
E proguardeastcoast@proguardsafety.com
A-61, Jalan Seri Setali 2, Off Jalan Air Putih, 25300 Kuantan, Pahang, Malaysia.

SOUTHERN Branch :

T +607 353 0780 (Hunting Line) F +607 354 9086
E proguardsouthern@proguardsafety.com
6, Jalan Molek 2/5, Taman Molek, 81100 Johor Bharu, Johor, Malaysia.

EAST MALAYSIA Branch :

T +6085 615 211/ 616 211 F +6085 615 311 E pgem@proguardsafety.com
Lot 1830 & 1831, Eastwood Valley Industrial Park Phase 3,
Miri By Pass Road, 98000 Miri, Sarawak, Malaysia.

PROGUARD SAFETY (NORTHERN) SDN. BHD. (592968-H)

T +604 288 8181 (Hunting Line) F +604 288 8188/ 288 8189
E proguardnorthern@proguardsafety.com
13-G, 13-1, 13-2, Vantage Point, Jalan Lenggong, 11600 Jelutong, Penang, Malaysia.

SRI MANJUNG Branch :

T +605 688 7348 (Hunting Line) F +605 688 7343
E pgsm@proguardsafety.com
13, Persiaran PM 3/2, Pusat Bandar Seksyen 3, 32040 Sri Manjung, Perak, Malaysia.

