130105
NorTorque Adjustable Mechanical Torque Wrench with Push Through Ratchet 1/2" Square Drive 60 - 300 N·m / 45 - 220 lbf·ft

PRODUCT DETAILS

- Durable, reliable and accurate mechanism
- Micrometer scale for simple and error free setting (on dual scale wrenches, the micrometer increment applies to the N·m scale)
- Light and fast adjustment saves operator time and effort
- Clicking system triggers a tactile and audible signal
- Secure push/pull locking mechanism is quick and intuitive to use and prevents accidental adjustment
- Convenient hanger feature for tool storage also aids wrench unlocking and adjustment
- Push-through ratchet allows clockwise and counter-clockwise operations
- Tough ratchets with narrow engagement angles allow for easy positioning of the tool in confined spaces (5° for models up to 200 N·m and 6° for models 300 N·m and above)
- Handle centre or calibration force point marked on handle
- Accuracy to ±3% meets the requirements of ISO 6789-1:2017
- Supplied with a Declaration of Conformance
- Made in the UK





PRODUCT ATTRIBUTES

Product: 130105

N·m	60-300 N·m	lbf·ft	45-220 lbf·ft		1/2 in
lbf·ft	5 lbf·ft	A	587 mm	B	562 mm
C	460 mm	D	52 mm	E	45 mm
F	25 mm	kg	1.4 kg		