Pushing Performance
Since 1945

Han-Modular Flexbox hood 3 entries

Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 8013
Specification	Han-Modular Flexbox hood 3 entries
HARTING eCatalogue	https://harting.com/09140008013

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Modular® Flexbox
Type of hood/housing	Hood

Version

Version	Top entry
Number of cable entries	3
Cable entry	3x

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP54
Clamping range	5 ... 24 mm

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-2) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984 EN 45545-1 EN 45545-2

Commercial data

Packaging size	1
Net weight	109.6 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140182011
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com