



PRODUCT-DETAILS

PACS28/BL/50M**28MM PA6 CONDUIT 50M - BL****General Information**

| | |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type: | PACS28/BL/50M |
| Product ID: | 7TCA296000R1990 |
| EAN: | 5020963000843 |
| Catalog Description: | 28MM PA6 CONDUIT 50M - BL |
| Long Description: | Standard Weight Conduit, Nominal Conduit Size 28mm, NW Conduit Size 23, Coarse Conduit Pitch, Outside Diameter 28.5mm, Inside Diameter 21.7mm, Static Bend Radius 50mm, Reel Length 50 Meters, Polyamide (Nylon) 6, Black |
| Display Name: | PACS28/BL/50M |

Eco Transparency

Environmental Product Declaration - EPD: 9AKK108469A9306

Additional Information

| | |
|---------------------------|--------------------------------------------------------------|
| Product Main Type: | Adaptaflex Flexible Cable Protection |
| Application: | Indoors / Outdoors - Light Industrial, Buildings & Machinery |

Ordering

| | |
|-------------|---------------|
| EAN: | 5020963000843 |
| UPC: | 786210267586 |

Dimensions

| | |
|--------------------------|---------|
| Outside Diameter: | 28.5 mm |
|--------------------------|---------|

Technical

| | |
|-----------------------------|-------------------|
| Number of Batteries: | 0 |
| Color: | Black |
| Material: | Polyamide/Nylon 6 |

Environmental

| | |
|--------------------------|------------------------------------------------------------------------|
| WEEE Category: | Product Not in WEEE Scope |
| RoHS Information: | Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019 |

Container Information

| | |
|----------------------------------------|--------------------|
| Package Level 1 Units: | 1 piece |
| Package Level 1 EAN: | 5020963000843 |
| Package Level 1 Height: | 9.06 in 230 mm |
| Package Level 1 Depth / Length: | 24.02 in 610 mm |
| Package Level 1 Width: | 24.02 in 610 mm |

Certificates and Declarations

| | |
|----------------------------------------|-----------------|
| Declaration of Conformity - CE: | 9AKK107492A9618 |
| RoHS Declaration: | 9AKK107992A8994 |
| REACH Declaration: | 9AKK107992A8994 |

External Classifications and Standards

| | |
|----------------|------------------------------------|
| ETIM 8: | EC001175 - Corrugated plastic hose |
| ETIM 9: | EC001175 - Corrugated plastic hose |

UNSPSC:

39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

