Pneumatic disc brake piston pushing/turning tool

Description:

● Pneumatic jack pushing and turning the piston
● Can be used for right or left turning pistons
● Max pressure 6.2 bar 1/4 NPT. Ø 10 mm 3/8” Set comprising:
● 1 pneumatic tool DF.17.
● 7 cups: DF.6-2P, DF.6-3P, DF.6-5, DF.6-9, DF.6-14, DF.6-15, DF.6-16.
Examples of allocation:
● DF.6-5: BMW Series 7 - Honda Accord - Mercedes Class B - Toyota Land Cruiser...
● DF.6-9: Mini Cooper - Toyota Auris.
● DF.6-14: Iveco Daily.
● DF.6-15: Renault Scenic, Laguna.
● DF.6-16: Renault Master 3 phase I.
● Supplied in a plastic case with operating instructions and application guide.

	Weight [g]
DF.17-P	2900.0

© FACOM 2020