

technical hotline +44 (0)1268 563720

surface | wiring devices

Switches

 UNSWITCHED
 FUSED
 SURFACE

 10 AMP
 SURFACE


K932ALM



K972ALM



K972D6ALM



K3072WHI



K954ALM



K983ALM



K989ALM



K986ALM



K3054WHI



K3086WHI



K3591ALM



K3592ALM



K3593ALM



K3091WHI



K3092WHI

K932ALM
 DP SWITCHED
 WITH FLEX OUTLET

K972ALM
 DP SWITCHED
 WITH FLEX OUTLET
 AND NEON

K972D6ALM
 DP SWITCHED
 WITH FLEX OUTLET,
 NEON AND
 RED ROCKER

K3072WHI
 DP SWITCHED
 WITH FLEX OUTLET,
 NEON
 WITHOUT BOX

10

K954ALM
 UNSWITCHED

10

K954KOALM
 UNSWITCHED WITH TAMPERPROOF
 FUSE CARRIER SCREW

1

K983ALM
 UNSWITCHED WITH NEON

5

K989ALM
 UNSWITCHED WITH FLEX OUTLET

5

K989D1ALM
 UNSWITCHED WITH FLEX OUTLET
 AND FITTED WITH 5 AMP FUSE

5

K986ALM
 UNSWITCHED WITH FLEX OUTLET
 AND NEON

5

 All connection units are fitted with
 a 13A fuse (to BS 1362.)

 Earth terminal fitted
 in base of the box.

 DIMENSIONS:
 86 x 86 x 47mm

 TERMINAL CAPACITY:
 2 x 6mm² stranded (max)

 KNOCKOUTS:
 6 x 20mm.

 Two in one side and one in each of
 other three sides, one in base.

 Spare Boxes with and without
 knockouts are available.

All boxes have a base knockout.

BS 1363 Pt.4: 1995

K3054WHI
 UNSWITCHED
 WITHOUT BOX

10

K3086WHI
 UNSWITCHED WITH
 FLEX OUTLET AND NEON
 WITHOUT BOX

10

K3591ALM
 1 GANG SP
 TWO WAY

5

K3592ALM
 2 GANG SP
 TWO WAY

5

K3593ALM
 3 GANG SP
 TWO WAY

5

K3091WHI
 1 GANG SP
 TWO WAY
 WITHOUT BOX

10

K3092WHI
 2 GANG SP
 TWO WAY
 WITHOUT BOX

10

 These switches do NOT have to be
 derated when used with fluorescent
 or inductive loads.

 An earth terminal is fitted in each
 box.

 DIMENSIONS:
 86 x 86 x 47mm

 TERMINAL CAPACITY:
 1 x 6mm² (max)

 KNOCKOUTS:
 6 x 20mm.

 Two in one side and one in each of
 other three sides, one in base.

 Spare Boxes with and without
 knockouts are available.

All boxes have a base knockout.

BS EN 60669-1: 1999