SAM
CRÉATEUR D'OUTILS

COMPOSITION OF 380 TOOLS IN FOAM MODULES FOR TROLLEYS

CP-380MM

SAM Outillage
10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France
RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬
https://www.sam-outillage.com/

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:28



DESCRIPTION

COMPOSITION OF 380 TOOLS IN FOAM MODULES FOR TROLLEYS

Composition of 380 foam module tools for 41 series tool chest or others.

SPECIFIC DATA

Designation	380 TOOLS IN FOAM MODULE
Sales reference	CP-380MM
Weight (kg)	34.54
Guarantee	O | SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.
Guarantee without time limit on the tools used under normal conditions.

>> Find out more

Toolset

x 1 Selection of tightening tools - foam module 3/3
CP-138PM

x 1 Screw driving bits ph + hex
E-900J10
Ref : E-900J10

x 1 Screw driving bits pz +tx
E-910J10
Ref : E-910J10

x 1 Screw driving bits fte +txr
E-920J10
Ref : E-920J10

x 1 3/8" sliding handle
J-120
Ref : J-120

x 1 1/2" site ratchet with lever reversion
J-157B
Ref : J-157B

x 2 Straight 3/8" extensions
J-2...
Ref : J-208 - J-210

x 1 3/8" joint
J-240
Ref : J-240

x 17 3/8" short hexagonal sockets in mm
JH-...
Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22

x 2 LONG SOCKET 6-FLAT 3/8" 28 MM
JHL-...
Ref : 16 - 21

x 5 3/8" sockets for Torx® head
JTX-...
Ref : 10 - 11 - 12 - 14 - 16

	x 15	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 3,5 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15
	x 1	1/4" sliding handle R-120 Ref : R-120
	x 1	Site 1/4" rachet R-157B Ref : R-157B
	x 2	Straight 1/4" extensions R-21... Ref : R-210 - R-211
	x 1	Flexible 1/4" extension R-220 Ref : R-220
	x 1	Fitted 1/4" extension R-225 Ref : R-225
	x 1	1/4" joint R-240 Ref : R-240
	x 1	1/4" bit holder socket RD-1 Ref : RD-1
	x 6	1/4" single-piece screwdriver sockets for hollow hexagonal screws RS-... Ref : 3 - 4 - 5 - 6 - 7 - 8
	x 1	Sets of 6 screwdriver sockets 1/4" for 6-flat socket head screws on storage rack RS-J6R Ref : RS-J6R
	x 1	Set of 8 screwdriver sockets 1/4" for Torx® imprint on storage rack RT-J8R Ref : RT-J8R
	x 5	1/4" sockets for Torx® head RTX-... Ref : 4 - 5 - 6 - 7 - 8
	x 1	1/2" sliding locking handle S-120 Ref : S-120
	x 1	1/2" site ratchet with lever reversion S-157B Ref : S-157B

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:28

x 1

Straight 1/2" extensions
S-2...
Ref : S-215

x 1

1/2" joint
S-240
Ref : S-240

x 18

1/2" short hexagonal sockets in mm
SH-...
Ref : 10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32

x 5

1/2" long bi-hexagonal sockets in mm
SL-...Douilles_MM
Ref : 14 - 15 - 17 - 19 - 22

x 3

1/2" sockets for Torx® head
STX-...
Ref : 18 - 20 - 24

x 1

3/3 FOAM MODULE 12 PLIERS
CP-12MM

x 1

Polished chrome-plated universal pliers with spring
204-R...G
Ref : 204-R18G

x 1

Mechanic's diagonal chrome-plated cutting pliers with spring
232-R...G
Ref : 232-R18G

x 1

Straight half-round nose pliers, polished chrome-plate
237-...G
Ref : 237-20G

x 1

Polished chrome-plated angled half-round nose pliers with spring
239-R20G

x 1

Mat chrome-plated straight nose outer circlips pliers
195-...A
Ref : 195-17A

x 1

Mat chrome-plated 90° elbowed nose outer circlips pliers
196-...A
Ref : 196-17A

x 1

Burnished finish straight nose inner circlips pliers
190-...A
Ref : 190-17A

x 1

Mat chrome-plated 90° elbowed nose inner circlips pliers
191-...A
Ref : 191-17A

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:28

x 1

High-capacity lock grip pliers
212-25

x 1

Crimping pliers
241-42

x 1

Polished chrome-plated stacked-branch multigrip pliers
209-25B

x 1

Mechanic's end nippers
229-...
Ref : 229-25

x 1

MODM 3/3 88 SCREWDRIVER+WRENCHES MA.
CP-88MM

x 1

Flexible screwdriver 6 mm
23-...
Ref : 7 mm

x 1

Ratchet telescopic screwdriver with magnetic bit holder
T-PE

x 9

Rack of 9 male 6-flat keys with spherical head in mm
67-AR9A
Ref : 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm

x 9

Rack of 9 Torx® male keys
66-R9A
Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40

x 9

Torx® S1 round blade screwdriver
T-...X
Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40

x 2

Testing screwdriver
268-...
Ref : 6-24V et 100-500V

x 3

SCREWDRIVER ELECTRICIAN INSULATED 1000V
ZTC-...E
Ref : N°2 - N°3 - N°4

x 2

SCREWDRIVER PHILLIPS® INSULATED 1000V
ZTC-...P
Ref : N°1 - N°2

x 1

Electrician's S1 round blade slotted head screwdriver
T-...E
Ref : 4x100 mm

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:28

x 3

Mechanic's S1 round blade slotted head screwdriver
T-...M
Ref : 5,5x100 - 6,5x100 - 8x150 mm

x 3

Phillips® S1 round blade screwdriver
T-...P
Ref : N°1 - N°2 - N°3

x 1

Phillips® S1 round blade tom thumb screwdriver
T-...P_Tom_pouce
Ref : N°2

x 1

Electrician's S1 round blade tom thumb slotted head screwdriver
T-...E_Tom_pouce
Ref : 6,5x35 mm

x 30

31-piece screwdriver bit set
E900-J30B

x 1

3/3 FOAM MOD 24 STRIK TOOLS
CP-24MM

x 1

SAMSOPLUS® riveting hammer, three-material handle
310-...TM
Ref : 32 mm

x 1

Mallets with interchangeable tips
320-...D
Ref : 32 mm

x 1

Short tape measures with two-material casings
UB-...N
Ref : 2 m

x 1

Slide callipers with 1/2"0 mm precision
710-P-8

x 1

Plastic body scriber
665-11

x 6

Short drift punches
7-C...A
Ref : 1,9 - 2,9 - 3,9 - 4,9 - 5,9 - 7,9 mm

x 1

Knife with retractable blade
378-7

x 5

Set of 5 helix pullers
761-C-5

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:28

x 1

Fitted flat hand file
LPM-...E
Ref : 250 mm

x 1

Fitted round files
LR-...-E
Ref : 250 mm

x 1

Fitted half-round files
LDR-...-E
Ref : 250 mm

x 2

Constant section chisels with comfortable handle
3-...-G
Ref : 175 - 200 mm

x 1

Punch 10 mm
8N-...A
Ref : 8 mm

x 1

3/3 FOAM MOD 40 WRENCHES
CP-40MM

x 19

Extra-thin combination wrench
50N-...
Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 mm

x 9

Set of 9 multi-nut inch / metric ratchet combination spanners
50-HCJ9
Ref : 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 mm

x 8

Set of 8 offset ring wrenches in mm
105-J8D

x 4

Torx® polygonal straight wrench
9T-...
Ref : E6xE8 - E10xE12 - E14xE18 - E20xE24 mm

x 1

MODM 3/3 78 SOCKET+SCREWDRIVER
CP-78MM

x 10

Set of sockets for rounded nuts and pins
74NJ-J10
Ref : 6 - 8 - 10 - 11 - 12 - 13 - 14 - 15 - 17 - 19 - 21 - 24 - 27 mm

x 9

1/2" short hexagonal sockets in mm
SH-...
Ref : 10 - 11 - 12 - 14 - 16 - 18 - 20 - 22 - 24 mm

x 5

Socket sets 1/2" long impact car wheel nuts
19141-95
Ref : 15 - 17 - 19 - 21 - 22 mm

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:28

	x 10	1/2" long hexagonal impact sockets in mm NS-...L Ref : 10 - 12 - 13 - 14 - 15 - 19 - 21 - 22 - 30 - 32 mm
	x 1	Shock socket extra-long slim 1/2" " 19141-...M Ref : 36 mm
	x 7	1/2" screwdriver socket - hexagonal SC-...1/2_6_pans Ref : H5 - H6 - H7 - H8 - H10 - H12 - H14
	x 8	1/2" Torx® screwdriver socket ST-...-... Ref : T25 - T27 - T30 - T40 - T45 - T50 - T55 - T70
	x 10	1/2" XZN® screwdriver socket SD-...-... Ref : L55 : M6 - M8 - M10 - M12 - M14L100 : M6 - M8 - M10 - M12 - M14
	x 8	1/2" ribes screwdriver socket SR-... Ref : L100 : RB5 - RB6 - RB7 - RB8 - RB10 - RB12L200 : RB8 - RB9

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:28