SIEMENS

Data sheet 3SE6704-1BA

Solenoid round M30

product brand name	SIRIUS
product designation	Magnetically operated switch
design of the product	Coded magnet, round
product type designation	3SE67
General technical data	
product feature	M30
protection class IP	IP67
Substance Prohibitance (Date)	01.07.2006
length of the sensor	15 mm
diameter of the sensor	30 mm
mechanical installation condition for sensor	no flush installation possible
Enclosure	
design of the housing	cylinder, thread
material of the enclosure	plastic
Safety related data	
category acc. to EN 954-1	4
Ambient conditions	
ambient temperature during operation	-25 ... +70 °C
Installation/ mounting/ dimensions	
fastening method	screw fixing
Certificates/ approvals	

General Product Approval	EMC	Declaration of Conformity
UL, EAC, EAC, RCM, CE EG-Konf.		UK Declaration of Conformity

other	Dangerous Good
Confirmation	Transport Information

Further information
Information- and Downloadcenter (Catalogs, Brochures,…)

Subject to change without notice
© Copyright Siemens

https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE6704-1BA
Cax online generator
http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE6704-1BA
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3SE6704-1BA
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE6704-1BA&lang=en

last modified: 12/23/2020

Subject to change without notice
© Copyright Siemens