1635-S Closed end connector terminals, for free connections

CE

Insulating housing: transparent polycarbonate UL94 V0
Conductive body: brass
Captive screw: galvanized steel
Self-extinguishing: EN60695-2-10 a 850°C, EN 60335-1:2002 +A2:2006, EN60695-2-11
Working temperature: max. 85 °C
Degree of protection: IP20
Reference standards: EN60998-1: EN60998-2-1:2004





Stated prices are for individual 10-way bars. Minimum quantity: 10 pcs

	art.	mm²	mm²	L mm	L1 mm	S mm	N
BM9961	BM9961	35 25 16	35	43.5	26.1	49.4	2 2÷3 2÷4
BM9960	BM9960	25 16 10	25	36.3	22.5	41.9	2 2÷3 2÷4
BM995	BM995	16 10 6	16	31.8	18.8	32.2	2 2÷3 2÷4
BM994	BM994	10 6 4	10	26	14.7	26	2 2÷3 2÷4
BM993	BM993	6 4 2.5	6	22.5	11.8	23	2 2÷3 2÷4
BM9924	BM9924	4 2.5 1.5	4	21	10.3	20	2 2÷3 2÷4
BM992	BM992	2.5 1.5 1	2.5	17.5	9	18.2	2 2÷3 2÷4
BM991	BM991	1.5 1 0.75	1.5	15	7.5	14.5	2 2÷3 2÷4