SAUTER **TVP-L**

Manual test stand for compressive force measurements with digital length measurement

Category

Brand	Sauter
Product category	Test bench
Product group	Manual test stand
Product family	TVP-L

Measuring System

Measurable length [Max]	10 cm
Tolerance (measured length)	2%

Construction

Dimension (W×D×H)	150×233×420 mm
Dimension housing (W×D×H)	150×233×420 mm
Dimensions completely mounted (W×D×H)	150×233×420 mm
Material housing	metal, lacquered
Type of drive	manual lever
Mounting - force dissipation	5 × threaded hole M6
Mounting - force application	5 × threaded hole M6
Generated force [Max]	500 N
Measuring room height [Max]	315 mm
Traverse distance with lever movement / release [Max]	78 mm

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	570×275×240 mm
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	12 kg
Shipping weight	12 kg
Shipping volume weight	7,5 kg

Product information

GTIN/EAN number	4045761139763
Trade number	90248000
REACH classification	no prohibited substances

Pictograms

STANDARD