# GeoTape 2in1

## New 20m Laser distance measure with built in 5m steel tape.

| TECHNICAL DATA | |
|---|---|
| ART.-NO. 300710 | |
| Laser measuring range | up to 20m |
| Accuracy | ± 2 mm |
| Resolution | 1 mm |
| Tape length | 5m |
| Tape accuracy | ± 1,5 mm @ 5m |
| Blade width | 19 mm |
| Auto switch-off Laser/Display | 30 / 180 seconds |
| Laserclass / Wavelength | 2 / 630-670 nm |
| Working temperature | 0 to 40°C |
| Power supply / working time | Li-Ion / 5 h |
| Battery charging | via USB connection |
| Dimensions | 83 x 79 x 54 mm |
| Weight (with batteries) | 275g |

**FEATURES**

- Length and area measurement
- Laser measurement reference is always at the rear
- Independent use of Laser and Tape measure
- Magnetic end hook
- Positive toggle lock to secure blade at any length
- Metal belt clip
- Cover-protected USB port
- Concealed ON/OFF button to prevent mis-operation
- Auto switch-off to prolong battery life

**SUPPLIED WITH**

- USB charging cable
- Built-in Li-Ion battery

0800 292 2188
TradeSurvey.co.uk Sales@TradeSurvey.co.uk
TRADE SURVEY