BOT LIGHTING
FOR A BRIGHT FUTURE

OPAL A60

ELD1016X2

14,5 W - 1921lm - 2700K

15.000 H | NOT DIMMABLE | INSTANT



DIMENSIONS	A	B	C
1	120	---	60

GENERAL INFORMATIONS	
Code	ELD1016X2
Ean	8031453019709
Family	OPAL A60
Technology	LED
Energy class	A++
Operating temperature (° C)	-20 - +40

PACKAGING	
Packaging	BOX
Pack	10 / 50

LIGHTING DATA	
Kelvin (°)	2700
Lumen	1921
Beam (°)	200
Luminous ef(cacy (lm / W)	86,11
Color rendering (CRI)	>80

TECHNICAL FEATURES	
Base	E27
Power (W)	14,5
Equivalence (W)	121
Supply voltage (V) / Max (V)	220 / 240
Power frequency (Hz)	50/60
Power factor	>0,55
Dimmer compatibility	NO

Bot Lighting srl
Via Lombardia, 37/39 – 30030 Cazzago di Pianiga (VE) Italy - T. +39.041.51.29.411 – F. +39.041.51.01.715
www.botlighting.it – ordini@botlighting.it – info@botlighting.it