





LED PL Glass TC-DEL G24q 4P 9W (26W) 1350lm 840 AC

Article number: 146753

BAI LED PL Glass G24q 4-pins TC-DEL 9W (26W) 4000K Frosted 1350lm 230V-240V 360° 35x168mm Temp. -20°C +40°C LED-lamp Alt PLC Dulux D

The LED PL Glass G24q (4-pin) TC-DEL lamps are replacements for the often used compact fluorescent lamps without integrated ballast. PL stands for PubLic as these lamps are mainly used in public spaces, corridors, offices and as orientation lighting. This PL LED series has the same shape and size as its fluorescent predecessors. In addition, just like their predecessor, they are made of glass, which ensures the same uniform light image. They are therefore a 1-on-1 sustainable replacement. Connect directly to mains voltage (AC). Not for use with Electronic Ballast (HF/ECG), disconnect ballast before use! Always read the manual carefully before installation.

General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	LED PL Glass TC-DEL G24q 4P 9W (26W) 1350lm 840 AC
Brand	Bailey
Productseries	LED PL Glass
Producttype	G24Q 4P 840

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

LED PL Glass TC-DEL G24q 4P 9W (26W) 1350lm 840 AC

Article number: 146753

ETIM specifications

Socket	G24q
Luminous flux [lm]	1350 - 1350
Nominal voltage [V]	220 - 240
Lamp power [W]	9 - 9
Colour temperature [K]	4000 - 4000
Diameter [mm]	35
Length [mm]	168
Dimmable	No
Lamp shape	Tube, single-ended
Beam angle [°]	360 - 360
Colour	White
Type of glass/cover	Opal
Lamp designation	Other
Colour rendering index CRI	80-89
Voltage type	AC
Filament lamp	No
Rated luminous flux according to IEC 62612 [lm]	1350
Power factor	0.5
Lamp efficacy [lm/W]	139
Nominal current [mA]	70 - 70
Colour of light according to EN 12464-1	Neutral white 3300-5300 K
Housing colour	White
Average nominal lifetime [h]	30000
Degree of protection (IP)	IP20
Colour consistency (McAdam ellipse)	SDCM5
Min. number of switching cycles	15000
Weighted energy consumption in 1000 hours [kWh]	9
Remote operation possible	No
With movement sensor	No
With remote control	No
Photobiological safety according to EN 62471	RG0
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for electronic ballast	No
Suitable for magnetic ballast	Yes
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming Touch and Dim	No
Dimming Zigbee	No

Bailey Electric & Electronics bv | Everdenberg 21 | 4902 TT Oosterhout | nl | +31 (0)162 52 24 46 | info@bailey.nl

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

Dimming Bluetooth	No
Dimming Wi-Fi	No
Energy efficiency class according to EU regulation 2019/2015	D
With twilight switch	No
Material of light bulb	Glass

Alternative articles



143162

LED PL TC-DEL G24q 4P 10W (26W) 1000lm 840 FR AC

All rights reserved. We reserve the right to change designs and technical specifications of our products.s