



Oil



Heavy Duty

Heavy-duty work gloves, providing good defense against oils, liquids and abrasion

- **Heightened durability:** Three-quarter-coated in nitrile, EDGE[®] 48-501 cut and sewn heavy-duty work gloves grant long-lasting performance and a good level of protection against abrasion
- **Reinforced protection:** These cost-effective nitrile gloves are not only stronger and more flexible than PVC, they also fend off oils, greases and liquids in oily and wet environments
- **Economical choice:** EDGE[®] 48-501 safety gloves are a cost-effective choice to protect workers from workplace risks and help them to perform heavy-duty tasks more effectively
- **Food handling compliance:** Owing to their FDA-compliant materials, these protective gloves are suitable for food contact and packaging



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Recycling and Waste Disposal

Applications

- Cold plastic moldings
- Heavy-duty cables
- Rough casting and cores
- Steel bars, sheet metals, cans and other metal products
- Street cleaning and refuse collection

Key Features

- **Three-quarter dipped nitrile coating:** Added robustness and durability
- **Oil and liquid repellence:** Safer heavy handling in slippery conditions
- **Cost-effective:** Quality yet affordable hand protection gloves

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



4111B

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE® 48-501	Finishing: ¾ Coated Coating Material: Nitrile Liner Material: Cotton Cuff Style: Knitwrist		8, 9, 10, 11	252-280 mm, 9.9-11.0 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699