SAUTER **CK 10-Y4**

Flat miniature alloy steel load cell



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CK Y4

Measuring System

Weighing capacity [Max]	40 kg
Load cell - characteristic value - nominal	0,5 mV/V
Load cell - characteristic value - variance	0,05 mV/V
Load cell OIML class	C1
Load cell connection	4-wire
Power supply + Colour	red
Power supply - Colour	black
Signal + Colour	green
Signal - Colour	white
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Directions of force	compression
Load sell - Input resistance - nominal	1000 Ω
Load cell - Output resistance - nominal	1000 Ω
Load cell - Input resistance - variance	10 Ω
Load cell - Output resistance - variance	10 Ω
Load cell - Recommended exitation voltage [Min]	3 V
Load cell - Recommended exitation voltage [Max]	10 V
Load cell - Isolation resistance - [Min]	2000 MΩ
Load cell - Combined error	0,05%
Temperature coefficient - characteristic value	± 0.1% F.S. / 10 °C
Zero balance	± 0,3mV/V
Temperature coefficient - zero signal	± 0.1% F.S. / 10 °C
Creep error (30 minutes)	± 0.05% F.S.
Safe overload	120%
Ultimate overload	150%

Functions

IP protection - complete device	IP65

Construction

Material	steel, galvanized
Design	Miniature bending beam
Dimension (W×D×H)	34×34×4,5 mm
Cable length	0,45 m
Mounting - force application	Support point
Mounting - force dissipation	4 × through hole Ø 3,1 mm

Environmental conditions

Ambient temperature [Min]	-20 °C
Ambient temperature [Max]	50 °C
Use temperature [Min]	-10 °C
Use temperature [Max]	60 °C
Storage temperature [Min]	-30 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓

Product information

GTIN/EAN number	4045761246393
Trade number	84239010
REACH classification	no prohibited substances

Packing & Shipping

Shipping method	Parcel service
Delivery time	1 d
Dimensions packaging (W×D×H)	90×90×20 mm
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping volume weight	0,1 kg

SAUTER **CK 10-Y4**

Flat miniature alloy steel load cell

Pictograms

STANDARD