LED S14s 30X1000 DIM 13W (87W) 1270lm 827 Opal

Article number: 145654

BAI LED S14s 30X1000mm 13W (87W) 1270lm 2700K Dimmable Opal 15000h LED-Lamp

Typical applications include bathrooms, mirrors, alcoves and kitchens. Ambient temperature: -10°C to +40°C.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	LED S14s 30X1000 DIM 13W (87W) 1270lm 827 Opal
Brand	Bailey
Productseries	LED Linear
Producttype	S14S 1000MM 827

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

LED S14s 30X1000 DIM 13W (87W) 1270lm 827 Opal

Article number: 145654

ETIM specifications

Socket	S14s
Luminous flux [lm]	1270 - 1270
Nominal voltage [V]	220 - 240
Lamp power [W]	13 - 13
Colour temperature [K]	2700 - 2700
Diameter [mm]	30
Length [mm]	1000
Dimmable	Yes
Lamp shape	Tube, double-ended
Beam angle [°]	200 - 200
Colour	White
Type of glass/cover	Opal
Lamp designation	Other
Colour rendering index CRI	80-89
Voltage type	AC
Filament lamp	No
Rated luminous flux according to IEC 62612 [lm]	1270
Power factor	0.9
Lamp efficacy [lm/W]	97
Nominal current [mA]	60 - 60
Colour of light according to EN 12464-1	Warm white < 3300 K
Housing colour	White
Average nominal lifetime [h]	15000
Degree of protection (IP)	IP20
Colour consistency (McAdam ellipse)	SDCM6
Min. number of switching cycles	15000
Weighted energy consumption in 1000 hours [kWh]	13
Remote operation possible	No
With movement sensor	No
With remote control	No
Photobiological safety according to EN 62471	RG1
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for electronic ballast	No
Suitable for magnetic ballast	No
Dimming phase cut-off (trailing edge)	Yes
Dimming phase cut-on (leading edge)	Yes
Dimming Touch and Dim	No
Dimming Zigbee	No

Bailey Electric & Electronics bv | Everdenberg 21 | 4902 TT Oosterhout | nl | +31 (0)162 52 24 46 | info@bailey.nl

All rights reserved. We reserve the right to change designs and technical specifications of our products.s

Dimming Bluetooth	No
Dimming Wi-Fi	No
Energy efficiency class according to EU regulation 2019/2015	F
With twilight switch	No

Alternative articles

146883

LED S14s 29X1000 DIM 9.8W (65W) 880lm 927 Opal Glass

Complementary articles



92600037499

Lampholder Set S14s White

All rights reserved. We reserve the right to change designs and technical specifications of our products.s