Product Information

2875QMP125P30-13

EAN 4031582302455

Walkway castor with integrated brake shoe for moving walkways, threadguards with integrated brake shoe, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, Wheel centre made of Polyurethane, Tread: Polyurethane, 4 tracks, selfcleaning between tracks, with threadguards, precision ball bearing, distances between tracks: approx. 4,5 mm, track width: approx. 4,0 mm. Designed for the following palletsize: track width: approx: 2,75 mm, groove width: approx. 5,7 mm, groove depth: > 10 mm.
Hint:
Load capacity 80 kg per castor on level and securely attached floors, 40 kg per castor on walkways. Please note that according to EN1929 only castors with a minimum wheel diameter of 120 mm can be used on walkways.

Technical Data

Wheel diameter	125 mm
Width of Tread	32 mm
Centre hole	13 mm
Offset	40 mm
Swivel Interference	205 mm
Overall height	153 mm
Temperature	- 40 / + 60 °C
Standard	EN 12530
Weight	0.731 kg
Swivel Radius	102.5 mm
Hardness of tread	D 59 Shore
Load capacity	80 kg
Load capacity (static)	160 kg

Roll performance	+ + + + +
Movement noise	+ + + + +
Attrition	+ + + + +
Corrosion resistance	+ + + + +

© Copyright 2015, TENTE International, www.tente.com, 21/12/2015

Product Information

2875QMP125P30-13

EAN 4031582302455





© Copyright 2015, TENTE International, www.tente.com, 21/12/2015