MULTI PORT WALL BRACKETS

NEW

Female thread wall bracket - Couplers and drain - ISO 6150 B profile - ID passage 6 mm

Technical characteristics

Operating pressure: 0 to 16 bar

Temperature: - 20°C to + 80°C

Construction: Aluminium



A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	Inlet BSPP female thread	Outlet	Parts Numbers
78	135	63	80	6,5	G 3/4	4 x ISI 06	**MF 104S4IS**
78	180	63	125	6,5	G 3/4	6 x ISI 06	**MF 104S6IS**
78	225	63	170	6,5	G 3/4	8 x ISI 06	**MF 104S8IS**
78	270	63	215	6,5	G 3/4	10 x ISI 06	**MF 104S10IS**

PREVOST UK - G, Tower Business Park, Commercial Rd, Darwen BB3 0FJ - United Kingdom
Tel. : (+44) 0844 800 2788 - Fax : (+44) 0844 800 2789 - E-mail : sales@prevost-ltd.co.uk - www.prevost.eu International = PREVOST SAS - - C.S. 90208 - 74942 ANNECY-LE-VIEUX CEDEX - France Tel. : +33 (4)50 64 04 45 - Fax : +33 (0)4 50 64 00 10 - E-mail : sales@prevost.eu- www.prevost.eu

This document is non-contractual. PREVOST reserves the right to modify the features of its range without prior notice.