FEATURES

- A range of fully welded, tubular framed mobile safety steps
- Wide base
- Double handrail
- Finished in a red epoxy powder coat
- Fixed rubber wheels and swivel castors
- Swivel castors retract
- Punched steel treads
- Suitable for use in a wide range of environments

RS PRO 5 Tread Steel Steps 1.25m Platform Height, Red

RS Stock No.: 412-024

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Heavy duty mobile steps from RS PRO are the perfect solution for safely accessing areas that are out of reach in a wide range of environments. The steps feature a robust fully welded design manufactured from steel, offering excellent durability and reliability. The steps feature punched steel treads and platforms, enhancing the grip and safety of the user. In addition, these heavy-duty steps include anti-slip rubber feet to prevent them from moving when in use. The steps also feature fixed rubber wheels and swivel castors that retract when pressure is applied, allowing the steps to be moved with ease yet remain stable when in use. The 5 tread model is also fitted with a safety bar to prevent misuse of steps when mobile, and when released, this lowers the steps to the floor, enabling the operator to safely use the steps. For an additional layer of safety and protection, the steps include a double hand rail to assist with ascending or descending. RS PRO heavy duty mobile steps are available with either 4 or 5 tread steps and are suitable for use in a wide range of environments.

What sizes are available?

- 412-034: 4 Tread Steps
- 412-024: 5 Tread Steps

General Specifications

Number of Steps	5
Material	Rubber, Steel
Colour	Red
Applications	Warehouse, Factory, Retail, Distribution, Automotive cleaning and maintenance

Mechanical Specifications

Overall Dimensions	2150mm x 840mm x 1095mm
Overall Height	2150mm
Overall Width	840mm
Overall Depth	1095mm
Weight	42kg

Platform Dimensions	
Height	1.25m
Width	550mm
Depth	400mm
Top Tread Width	550mm
Top Tread Depth	200mm

Product Description	Platform Height(mm)	Overall Size H x W x D(mm)	Weight(Kgs)	Tread Size W x D(mm)	Platform Tread Size W x D(mm)	Castors	Wheels	RS Stock No.
5 Tread Steps	1250	2150 x 840 x 1095	42	550 x 200	550 x 400	75mmØ	160mmØ	412024