

# Specifications



Photo is representative



## Eaton FAZ-C10/1-NA-SP

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Single package,Medium levels of inrush current are expected,10 A,10 kAIC,Single-pole,277 V,5-10X /n,Q38,50-60 Hz,Screw terminals,C Curve

### General specifications

<b>PRODUCT NAME</b>	Eaton FAZ branch protector
<b>CATALOG NUMBER</b>	FAZ-C10/1-NA-SP
<b>EAN</b>	4015081636334
<b>PRODUCT LENGTH/DEPTH</b>	4.5 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	0.2 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489 CSA Std. C22.2 No. 235
<b>CATALOG NOTES</b>	Positioned for medium inrush startup currents to provide protection for small transformers and pilot devices. Single packaging of single-pole curves B, C and D for select amperages only.



Powering Business Worldwide

## Physical Attributes

<b>NUMBER OF POLES</b>	Single-pole
<b>TERMINALS</b>	Screw
<b>TYPE</b>	UL 489 Industrial miniature circuit breaker - supplementary protector

## Miscellaneous

<b>APPLICATION</b>	Suitable for applications where medium levels of inrush current are expected
<b>QUANTITY</b>	38
<b>SPECIAL FEATURES</b>	Single package

## Performance Ratings

<b>AMPERAGE RATING</b>	10 A
<b>CIRCUIT PROTECTION</b>	C curve
<b>FREQUENCY RATING</b>	50-60 Hz
<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	5-10X /n
<b>VOLTAGE RATING</b>	277V

## Resources

CATALOGS	<a href="#">Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - FAZ-C10/1-NA-SP</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.